


CT Scanning System/CTスキャニングシステム




FPC/FFC-to-Board, Wire-to-Board



FH28K

For FPC and FFC
Robust Lock Design
Pitch: 0.5mm
No. of Pos.: 10-80




FH48

For Shielded FFC
Vertical
Pitch: 0.5mm
No. of Pos.: 20-68




FH55

PCIe Gen.4 (16Gbps)
For FPC
Pitch: 0.4/0.5mm
Mated Height: 1.5mm
No. of Pos.: 10-40



FH41


For Shielded FFC
Pitch: 0.5mm
No. of Pos.: 15-68



FX15

Wire-to-Board
Pitch: 1.0mm
Applicable Cable:
36-40 AWG (Thin Wire Coaxial Cable)
28-32 AWG (Discreet Cable)
Rated Current: 0.5A
No. of Pos: 21, 31, 41, 51

For X-ray Detection Part




FX18

16Gbps High Speed Transmission
Pitch: 0.8mm
Rated Current: 0.5A/Signal
3A/Power
No. of Pos.: 40-180




FX23/FX23L

Floating Connector
16Gbps High Speed Transmission
Pitch: 0.5mm
Stacking Height: 8-30mm
No. of Pos.: 20-120 (Signal)
4 (Power)



FX26

Floating Connector
Heat Resistance up to 140°C
Pitch: 1.0mm
Stacking Height: 15-25mm
No. of Pos.: 20-60
Rated Current: 0.5A



IX

IEC Standard, Cat.6A
10Gbps High Speed
Rated Current: 1.5A
Applicable Cable: 22-28 AWG



PQ50

Light Weight,
Non-waterproof Type
Rated Current: 19A Max.
No. of Pos.: 20-50
Applicable Cable:
14-28 AWG

For Control Boards



IT5

3 Piece BGA Connector
25Gbps High Speed Transmission
Stacking Height: 14-40mm
No. of Pos.: 100, 200, 300




HR41

IP68
Interface Connector
No. of Pos.: 3, 5
Rated Current: 38A Max.



DF60

Pitch: 10.16mm
No. of Pos.: 1-6
Rated Current: 65A Max.*
*Derating Curve,
Ambient Temperature of 25°C



DF22

Pitch: 7.92mm
No. of Pos.: 1-5
Rated Current: 30A Max.



DF33C

Pitch: 3.3mm
No. of Pos.: 2-12
Rated Current: 5A Max.