

## 1. Internal Connection (Wire-to-Board, FPC-to-Board)



Robust  
125°C

### ZE05

Rated Current:  
2A (All Pins Power Supply)  
No. of Pos.: 2-24  
AWG: 20-26



125°C

### ZG05HV


High Voltage 1,000V  
Rated Current: 1A  
No. of Pos.: 6  
AWG: 22-24



125°C

### HVH-280 Internal

Rated Current: 30A  
No. of Pos.: 2,3  
AWG: 12-14



125°C

### ZK1

Pitch: 2mm  
Rated Current: 1A  
No. of Pos.: 32

## 2. Internal Connection (Floating Board-to-Board)



**FunctionMAX**

140°C

Vibration Absorb

Floating Design

### FX26

Pitch : 1mm  
Stacking Height : 15-25mm

## 3. Interface Connection (Waterproof Wire-to-Wire)



125°C

### ZE064W

IP67/IP69K  
Rated Current: 2A  
(All Pins Power Supply)  
No. of Pos.: 8,14,24  
AWG: 20-22



120°C

### HVH-280 (Waterproof)

IPXXB/IPX9K  
Rated Current: 30A  
No. of Pos.: 2  
AWG: 12-14