



### 1. Internal Connection (Floating Board-to-Board)



**FunctionMAX**

140℃

Vibration Absorb

Floating Design

**FX26**

Pitch : 1mm

Stacking Height : 15-25mm

### 2. Internal Connection (Wire-to-Board, FPC-to-Board)



Robust

125℃

**ZE05**

Rated Current: 2A  
(All Pins Power Supply)  
No. of Pos.: 2-24  
AWG: 20-26



125℃

**ZH05**

Rated Current: 2A  
(All Pins Power Supply)  
No. of Pos.: 16,20,24,32  
AWG: 22-26



125℃

**ZG05HV**

High Voltage 1,000V  
Rated Current: 1A  
No. of Pos.: 6  
AWG: 22-24



125℃

**HVH-280 Internal**

Rated Current: 30A  
No. of Pos.: 2,3  
AWG: 12-14



125℃

**ZK1**

Pitch: 2mm  
Rated Current: 1A  
No. of Pos.: 32

### 3. Interface Connection (Waterproof Wire-to-Wire)



125℃

**ZE064W**

IP67/IP69K  
Rated Current: 2A (All Pins Power Supply)  
No. of Pos.: 8,14,24  
AWG: 20-22



120℃

**HVH-280 (Waterproof)**

IPXXB/IPX9K  
Rated Current: 30A  
No. of Pos.: 2  
AWG: 12-14